

Capsule Sinkers

Basket Sinkers

Part No.	Description	OEM Ref
PSCUSBSK-JP	Japanese Pharmacopeia Basket Sinker (This has same dimensions as sinker shown in USP)	12-3070 V
PSBSK008-01	8 Mesh Basket Sinker	–
PSBSK008-JP	8 Mesh Basket Sinker, Japanese Pharmacopeia Size	–
PSSNK008-VK	8 Mesh Basket Sinker with Lid	12-3062 V
PSSNK010-VK	10 Mesh Basket Sinker with Lid	12-3060 V
PSSNK040-VK	40 Mesh Basket Sinker with Lid	12-3064 V



PSCUSBSK-JP



PSBSK008-01



PSBSK008-JP



PSSNK008-VK



PSSNK010-VK



PSSNK040-VK

Pronged Sinkers

Part No.	Description	OEM Ref
PSCAPWHT-VK	3 Pronged Capsule Sinker	12-3050 V
PSMAGWHT-VK	3 Pronged Capsule Sinker with Magnetic Legs	12-3056 V
PSCAPWHT-SV	3 Pronged Capsule Sinker, 316 S.S.	–



PSCAPWHT-VK / PSMAGWHT-VK PSCAPWHT-SV

O-Ring Sinkers

O-ring sinkers feature an expandable rubber ring. This lets the capsule swell whilst still maintaining adequate sinking.

Part No.	Description	OEM Ref
PSCAPWHT-S99	O-Ring Sinker, 316 S.S.	8399 S



PSCAPWHT-S99

S = Sotax **V** = VanKel



Spiral Sinkers


Part No.	Description	OEM Ref
PSCAPWHT-TR	Time Release Capsule Sinker	–
PSCAPWHT-PC	Breath Film Sinker	–
PSCAPWST-15	4 Spiral Sotax Style 316 S.S. Capsule Sinker	8280
PSCAPWHT-04	4 Spiral PTFE Coated Capsule Sinker	–
PSCAPWHT-4S	4 Spiral 316 S.S. Capsule Sinker	–
PSCAPWHT-LG	4 Spiral PTFE Coated Capsule Sinker	–
PSCAPWHT-XL	4 Spiral PTFE Coated Capsule Sinker	–
PSCAPWST-18	5 Spiral Sotax Style 316 S.S. Capsule Sinker	7346
PSCAPWST-19	6 Spiral Sotax Style 316 S.S. Capsule Sinker	8283
PSCAPWHT-2S	6 Spiral 316 S.S. Capsule Sinker	–
PSCAPWHT-02	6 Spiral PTFE Coated Capsule Sinker	–
PSCAPWHT-XS	6 Spiral 316 S.S. Capsule Sinker	–
PSCAPWST-23	7 Spiral Sotax Style 316 S.S. Capsule Sinker	6881
PSCAPWST-31	10 Spiral Sotax Style 316 S.S. Capsule Sinker	7349



PSCAPWHT-TR



PSCAPWHT-PC



Type 316 Stainless Steel Wire


This wire is ideal for winding your own tablet sinkers, especially if you have non-standard sized tablets. It is the same high-quality wire used to construct the basket sinkers and spiral sinkers and is very easy to work with.

Part No.	Description	OEM Ref
PSWIRESK-VK	316 Stainless Steel Wire, 0.024" (0.6mm) Diameter, 50' (15m) Roll	12-3000

Extensive details on all sinkers and capsules – SEE OVERLEAF pages 14-15

Capsule Sinkers

Sinker Type	Part Number	Style	Material	Coating	Inside Diameter	
					(inches)	(mm)
BASKET	PSCUSBSK-JP	Basket, JP	316 S.S.	-	0.470	11.9
	PSBSK008-01	Basket, 8 Mesh	316 S.S.	-	0.620	15.7
	PSBSK008-JP	Basket, 8 Mesh	316 S.S.	-	0.410	10.4
	PSSNK008-VK	Basket, 8 Mesh	316 S.S.	-	0.788	20.0
	PSSNK010-VK	Basket, 10 Mesh	316 S.S.	-	0.788	20.0
	PSSNK040-VK	Basket, 40 Mesh	316 S.S.	-	0.788	20.0
PRONGED	PSCAPWHT-VK	3 Prong	Nylon / P.P.	-	0.200	5.1
	PSMAGWHT-VK	3 Prong	Nylon / P.P.	-	0.200	5.1
	PSCAPWHT-SV	3 Prong	316 S.S.	-	0.275 → 0.210	7.0 → 5.3
O-RING	PSCAPWHT-S99	O-Ring	316 S.S.	-	0.466	11.8
SPIRAL	PSCAPWHT-TR	Butterfly	316 S.S.	-	0.224	5.7
	PSCAPWHT-PC	Strip Film	316 S.S.	-	0.436	11.0
	PSCAPWST-15	Helix	316 S.S.	-	0.197	5.0
	PSCAPWHT-04	Helix	Music Wire	PTFE	0.385	9.8
	PSCAPWHT-45	Helix	316 S.S.	-	0.385	9.8
	PSCAPWHT-LG	Helix	Music Wire	PTFE	0.410	10.4
	PSCAPWHT-XL	Helix	Music Wire	PTFE	0.465	11.8
	PSCAPWST-18	Helix	316 S.S.	-	0.236	6.0
	PSCAPWST-19	Helix	316 S.S.	-	0.276	7.0
	PSCAPWHT-25	Helix	316 S.S.	-	0.370	9.4
	PSCAPWHT-02	Helix	Music Wire	PTFE	0.370	9.4
	PSCAPWHT-XS	Helix	316 S.S.	-	0.580	14.7
	PSCAPWST-23	Helix	316 S.S.	-	0.315	8.0
	PSCAPWST-31	Helix	316 S.S.	-	0.433	11.0
	WIRE	PSWIRESK-VK	Sinker Wire 50'	316 S.S.	-	-




CAPSULES				
Capsule Size	Length		Diameter	
	(inches)	(mm)	(inches)	(mm)
000	1.029	26.1	0.390	9.91
00E	1.012	25.7	0.336	8.53
00	0.917	23.3	0.336	8.53
0E	0.909	23.1	0.301	7.65
0	0.854	21.7	0.301	7.65
1	0.765	19.4	0.272	6.91
2	0.709	18.0	0.250	6.35
3	0.626	15.9	0.229	5.83
4	0.563	14.3	0.209	5.32
5	0.437	11.1	0.193	4.91



Inside Length		Wire Diameter		Max Capsule Size	No. of Coils	Weight (g)
(inches)	(mm)	(inches)	(mm)			
0.935	23.7	0.039	0.99	00	8	4.00
1.060	26.9	0.028	0.71	000	9	5.40
0.790	20.1	0.028	0.71	1	8	3.85
0.461	11.7	0.028	0.71	000	-	17.60
0.461	11.7	0.025	0.64	000	-	19.00
0.461	11.7	0.010	0.25	000	-	20.00
1.000	25.4	-	-	2	-	0.90
1.000	25.4	-	-	2	-	1.20
1.040	26.4	-	-	1 (min=3)	-	1.25
1.015	25.8	-	-	1	-	1.14
0.386	9.8	0.026	0.66	-	-	0.55
0.436	11.1	0.035	0.89	-	-	1.20
0.610	15.5	0.016	0.41	5	6	0.60
0.840	21.3	0.043	1.09	0	5	1.70
0.840	21.3	0.047	1.19	0	5	1.95
1.100	27.9	0.043	1.09	000	6.5	2.00
1.150	29.2	0.043	1.09	000	5.5	2.15
0.709	18.0	0.016	0.41	3	8.7	0.75
0.760	19.3	0.016	0.41	2	8	1.00
0.840	21.3	0.043	1.09	0	8.5	2.85
0.840	21.3	0.050	1.27	0	8.5	2.05
0.885	22.5	0.047	1.19	Special*	8.5	3.60
0.905	23.0	0.016	0.41	0	9	0.95
1.220	31.0	0.031	0.79	000	11.9	3.25
-	-	0.032	0.81	-	-	-

Need any further advice on sinkers?
Email sales@dissolutionaccessories.com



*The Maximum Capsule Size of PSCAPWHT-XS is described as "Special" because this sinker is often used in veterinary applications where the capsule diameter can be very large – this sinker has an inside diameter of 0.580" (14.7mm) to accommodate such capsules.

