



Reaction vessel bubbler



- Ideal for closing reaction mixture from the atmosphere
- Side arm to facilitate filling with mineral oil
- Bubblers have capacity of approx 5ml

Product Code	Cone size	Pack qty.
GB1/19	19/26	1
GB1/24	24/29	1
GB1/29	29/32	1

Capacity measurement to graduated fill line.



Reaction Vessel bubbler, with gas inlet



- Ideal for closing reaction mixture from the atmosphere
- With gas inlet to provide continuous flow of inert gas (N₂ or Ar) over the reaction
- Complete with detachable plastic hose connection to allow easy and safe attachment to 9mm flexible tubing
- Bubblers have capacity of approx 5ml

Product Code	Cone size	Pack qty.
GB2/19SC	19/26	1
GB2/24SC	24/29	1
GB2/29SC	29/32	1

Capacity measurement to graduated fill line.



Mini gas bubbler



- For use in inert atmosphere experiments
- Ideal for bubble counting
- Complete with detachable plastic hose connections to allow easy and safe attachment to 9mm bore flexible tubing

Product Code	Capacity (ml)	Pack qty.
GB3/SC	2	1